

BMK-10

ELECTRODE FURNACE CABINET – ELECTRODE DRYER WITH DIGITAL THERMOSTAT (WHEELED)

CAPACITY	10 PACK. – 1000 STICKS – 50 KG
HEIGHT	102-70 CM
LENGTH- WIDTH	45 x 67 cm
TEMPERATURE	0-400 °C
ELECTRIC POWER	3000 W
ELECTRIC VOLTAGE	380-400 V
TOTAL CURRENT	8 A
WEIGHT	80 KG

The main operating principle is to get factory output electrodes in high temperatures for shocking process and to keep them in lower temperature for keeping them dry.

The factory output electrodes are kept at 300 °C for 2 hours in order to complete the shocking process and then, the thermostat shall be taken back to 130 °C and the electrodes shall be left for resting process. The electrodes shall be taken into protection thermoses after the resting process and transported to the application side. After all the electrodes are used, the same procedure shall be carried out.



OUR COMPANY HAS ISO 9001:2008

ISO 18001 OHSAS, CE CERTIFICATES.

IF DESIRE TO BE CERTIFIED TÜRK-AK TS-EN ISO-IEC 17025 CAN DEVICES ARE MADE CALIBRATION

